

TECH LIFT 500

Adjustment overload

Remove the eight screws on the cover (Torx 15 M5 x 8), remove the cover (see picture 1)

Loosen the screws on the switch plate (M4 Allen head screws), now you can adjust the plate (see picture 2). Test the lift and adjust at needs, when the power switch is activated, a signal is heard and the small red light on top of the cover lights up.



Picture 1



Picture 2

Manufacturer:

TECHLINE
SWEDEN AB

Tech Line Sweden AB

Kyrkbacken 2

SE-507 90 Brämhult

Email: info@techline.nu

Phone: +46 (0)723 735506 or +46 (0)709 837972

Webpage: www.techline.nu

VAT-nr: SE559248058501